

**HOLEX®**
**Die stock, for die Ø × height: 38,1X12,7 mm**


## Order data

Order number	149300 38,1X12,7
GTIN	4045197857095
Item class	12L

## Description

### Version:

Steel handles galvanised and can be unscrewed. With 5 screws to clamp the die. **Up to size 65×25** of die-cast zinc, **from size 75×20** of steel.

### Application:

For direct mounting of solid and adjustable dies to EN 22568.

Norm: EN 22568

Metric thread: M8 – M20

Metric fine thread: M10 – M14

UNC thread: 7/16" – 3/4"

UNF thread: 7/16" – 3/4"

Whitworth thread: 1.1/2"

Whitworth pipe thread: G1/16" – G1/4"

## Technical description

UNF thread	7/16 – 3/4 inch
Whitworth thread	1.1/2 inch
Whitworth pipe thread	G1/16 – G1/4 inch
for die Ø	38.1 mm
Metric thread	M8 – M20
UNC thread	7/16 – 3/4 inch
Metric fine thread	M10 – M14
Overall length	310 mm

Height	12.7 mm
Norm	EN 22568