

HOLEX®
Die stock, for die Ø × height: 50,8X15,9 mm

Order data

Order number	149300 50,8X15,9
GTIN	4045197857125
Item class	12L

Description
Version:

Steel handles galvanised and can be unscrewed. With 5 screws to clamp the die. **Up to size 65×25** of die-cast zinc, **from size 75×20** of steel.

Application:

For direct mounting of solid and adjustable dies to EN 22568.

Norm: EN 22568

Metric thread: M18 – M27

Metric fine thread: M20 – M28

UNC thread: 5/8" – 1"

UNF thread: 5/8" – 1"

Whitworth thread: 2"

Whitworth pipe thread: G3/8" – G1/2"

Technical description

Overall length	495 mm
UNC thread	5/8 – 1 inch
Whitworth pipe thread	G3/8 – G1/2 inch
Metric fine thread	M20 – M28
UNF thread	5/8 – 1 inch
Height	15.9 mm
for die Ø	50.8 mm
Whitworth thread	2 inch

Metric thread	M18 – M27
Norm	EN 22568