

HOLEX®
Die stock, for die \varnothing × height: 65X25 mm

Order data

| | |
|--------------|---------------|
| Order number | 149300 65X25 |
| GTIN | 4045197857163 |
| Item class | 12L |

Description
Version:

Steel handles galvanised and can be unscrewed. With 5 screws to clamp the die. **Up to size 65×25** of die-cast zinc, **from size 75×20** of steel.

Application:

For direct mounting of solid and adjustable dies to EN 22568.

Norm: EN 22568

Metric thread: M27 – M36

Metric fine thread: M30×3 – M36×3

UNC thread: 1.1/8" – 1.3/8"

Whitworth thread: 1.1/8" – 1.3/8"

Overall length: 630 mm

Technical description

| | |
|-----------------------|--------------------|
| Whitworth thread | 1.1/8 – 1.3/8 inch |
| for die \varnothing | 65 mm |
| Metric fine thread | M30×3 – M36×3 |
| UNC thread | 1.1/8 – 1.3/8 inch |
| Metric thread | M27 – M36 |
| Overall length | 630 mm |
| Height | 25 mm |
| Norm | EN 22568 |

