

Plug gauge "Go" chrome H7, Nominal size Ø: 25mm



Order data

Order number	484040 25
GTIN	2050001675132
Item class	48B

Description

Version:

The "Go" ends of these working gauges have a **wear allowance** to DIN 7164.

"Go" end with hard chrome measuring faces. This increases the gauge life about 8 times.

Standard:

Toleranz und Abmaße nach **DIN EN ISO 1938-1, DIN 2245-1 und DIN 7164.**

Note:

- **Further intermediate sizes available on request or can simply be ordered at www.hoffmann-group.com, for instance No. 484000 size 82.**

Technical description

Tolerance zone	H
Standard	DIN 7150-2
Standard	DIN 7164
Quality	7
Type of gauge	"Go" plug gauge
Type of gauge	"No Go" gauge
Nominal size	25 mm
Calibration	M2
Type of product	Pug Gauge

Services

Calibration "Go" / "No Go" plug gauge maximum \varnothing 60 mm	028300 60
DAkkS calibration "Go" / "No Go" plug gauge maximum \varnothing 60 mm	028340 60