



Cutting disc Basic* 2 in 1, Disc Ø: 115mm



Order data

Order number	563600 115
GTIN	9003172228990
Item class	53T

Description

Version:

General-purpose cutting discs for cutting off sections, pipes etc. **Specification A46BF; 2 in 1**

Technical description

maximum speed	13300 min ⁻¹
Bore Ø	22.23 mm
Disc thickness	1.6 mm
Shape description	flat
Specification	A46BF
Disc Ø	115 mm
for material thicknesses	7.7 - 8 mm
Grinding medium code	A
Iron, sulphur and chlorine constituents	< 0.1 %

recommended approach angle	90 degrees
optimised for material	HSS
optimised for material	Steel
Propulsive equipment	Angle grinders
maximum circumferential speed	80 m/s
Type of product	Cutting disc

User data

	Suitability	V _c	ISO code
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
INOX	suitable only under restricted conditions		
Ti	suitable only under restricted conditions		
GG(G)	suitable only under restricted conditions		
Plastic, GRP	suitable only under restricted conditions		
dry	suitable		