

**Abrasive sleeve holder slit, conical shank 6 mm Ø, largest Ø×head length:
20X63mm****Order data**

Order number	553830 20X63
GTIN	4045197240552
Item class	52E

Description**Version:**

Slotted, resilient rubber body with steel shank. Ground outer face for best concentricity.

Technical description

largest Ø	20 mm
smallest Ø	14 mm
maximum speed	21000 min ⁻¹
Head Ø	5 mm
Head length	63 mm
Shape description	conical
Shank Ø	6 mm
Backing material	resilient rubber body
Type of product	Tool sleeve carrier