

# uvex

## Comfort safety glasses uvex i-vo, Lens tinting: GREY



### Order data

Order number	096515 GREY
GTIN	4031101256375
Item class	04U

### Description

#### Version:

The 2-component safety glasses include soft components at the nose, brow and ear to ensure high wearing comfort even when worn for long periods of work. Inclination and length of the **side arms are individually adjustable**. Excellent **resistance to chemicals** and **scratch resistance** on the outside. uvex supravision sapphire coating for additional **scratch resistance** and **resistance to chemicals** even on the inner surface. With dark frame and **grey lens** for **more protection in naturally intense light** (direct sunlight, reflected light). **Transmission: 23%**.

#### Standard:

EN 166 EN 172

Frame properties: Adjustable nose pads

Lens coating: resistant to chemicals

UV protection: UV400

Lens material: Polycarbonate

Lens identification: 5-2.5 W 1 FT

### Technical description

Manufacturer ID	9160.076
Lens material	Polycarbonate
Lens coating	resistant to chemicals
Transmission	23 %
Lens identification	5-2.5 W 1 FT
UV protection	UV400

Series	i-vo
Frame identification	W 166 FT CE
Frame properties	Side padding
Frame properties	Arm length adjustable
Frame properties	Arm inclination adjustable
Frame properties	Adjustable nose pads
Type of product	Safety glasses

## Accessories

Storage box	096920
Lenses for safety glasses i-vo No. 096515 Set of 5 pieces	096516
Wall attachment bracket for moist lens cleaning towelettes	096691
Retaining strap with width adjustment	096940
Glasses case Type	096930
Storage box	096921
Glasses cleaning station	096694
Lens cleaning towelettes 100 pieces	096690
Glasses case Type CASE	096932 CASE
Storage box	096910