



Burr Z3 - medium, with chip breaker, HSS, Type: C1020



Order data

Order number	540800 C1020
GTIN	4045197156082
Item class	52D

Description

Version:

Shank Ø 6 mm.

HSS burrs for difficult vibration applications. **Cylindrical ball nose shape** (WRC)

Application:

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

Technical description

Shape	C1020
Head Ø	10 mm
Shape description	Ball nose
Overall length	60 mm
Shank Ø	6 mm
Tooth type abbreviation	Z3
Type of cut	with chip breaker
Toothing grit designation	medium
Head length	20 mm
Series	Tooth configuration Z3
Tool material	HSS
Type of product	Burr

