

Garant**Clamp toolholder, left-hand, Shank / insert size: 32/12mm****Order data**

Order number	250007 32/12
GTIN	4045197861610
Item class	21T

Technical description

Insert size	12 mm
Screw for clamping claw	259021 1
suitable indexable insert	CN.. 1204..
Shim	259031 22
Shank size	32 mm
Overall length L	170 mm
Clamping claw	259038 4
Shim screw	259025 6
Functional width L ₄	40 mm
Head length L ₁	34 mm
ISO code toolholder	MCLNR/L 3232P12
Standard	Works standard
Application type	left-hand
Through-coolant	no
Setting angle κ	95 degrees
Application	External longitudinal turning

Application	External longitudinal turning
Type of product	Boring bar

Accessories

Clamping claw Type 4	259038 4
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15
Shim screw Type 6	259025 6
Screw for clamping claw Type 1	259021 1
Shim Type 22	259031 22
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500