

Garant
Clamp toolholder, left-hand, Shank / insert size: 32/16mm

Order data

| | |
|--------------|---------------|
| Order number | 250007 32/16 |
| GTIN | 4045197861634 |
| Item class | 21T |

Technical description

| | |
|---------------------------------|-----------------|
| suitable indexable insert | CN.. 1606.. |
| ISO code toolholder | MCLNR/L 3232P16 |
| Screw for clamping claw | 259021 1 |
| Shim | 259031 23 |
| Shim screw | 259025 7 |
| Insert size | 16 mm |
| Clamping claw | 259038 4 |
| Shank size | 32 mm |
| Head length L ₁ | 34 mm |
| Functional width L ₄ | 40 mm |
| Overall length L | 170 mm |
| Series | QuickTurn |
| Standard | Works standard |
| Application type | left-hand |
| Through-coolant | no |
| Setting angle κ | 95 degrees |

| | |
|-----------------|-------------------------------|
| Application | External longitudinal turning |
| Application | External longitudinal turning |
| Type of product | Boring bar |

Accessories

| | |
|--|-------------|
| Shim Type 23 | 259031 23 |
| PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15 | 674248 TX15 |
| Shim screw Type 7 | 259025 7 |
| Clamping claw Type 4 | 259038 4 |
| Screw for clamping claw Type 1 | 259021 1 |
| Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm | 659957 500 |