

**Garant**
**Lever lock toolholder, right-hand, Shank / insert size: 20/11 mm**

**Order data**

Order number	250612 20/11
GTIN	4045197861719
Item class	21T

**Technical description**

Insert size	11 mm
Shank size	20 mm
Shim punches pack	259047 3
Shim	259031 7
ISO code toolholder	PDNNR/L 2020K11
Functional width L <sub>4</sub>	10 mm
Shim pins pack	259044 4
Lever screw	259018 6
Overall length L	125 mm
Lever	259015 7
suitable indexable insert	DN.. 1104..
Head length L <sub>1</sub>	25 mm
Series	QuickTurn
Standard	Works standard
Application type	right-hand
Through-coolant	no

Setting angle $\kappa$	63 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

## Accessories

Lever screw Type 6	259018 6
PrecisionBit for hexagon, 1/4 inch E 6.3 Hexagon 2,5 mm	674242 2,5
Lever Type 7	259015 7
Shim Type 7	259031 7
Shim punches set 10 pieces Type 3	259047 3
Set of shim pins 10 pieces Type 4	259044 4
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500