

Garant**Lever lock toolholder, right-hand, Shank / insert size: 25/11 mm****Order data**

Order number	250612 25/11
GTIN	4045197861726
Item class	21T

Technical description

Head length L ₁	29 mm
Functional width L ₄	12 mm
Overall length L	150 mm
Lever	259015 7
Shim pins pack	259044 4
Shim punches pack	259047 3
Shim	259031 7
Lever screw	259018 6
suitable indexable insert	DN.. 1104..
Insert size	11 mm
ISO code toolholder	PDNNR/L 2525M11
Shank size	25 mm
Standard	Works standard
Application type	right-hand
Through-coolant	no
Setting angle κ	63 degrees

Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Lever screw Type 6	259018 6
Set of shim pins 10 pieces Type 4	259044 4
Precision Bit for hexagon, 1/4 inch E 6.3 Hexagon 2,5 mm	674242 2,5
Shim punches set 10 pieces Type 3	259047 3
Shim Type 7	259031 7
Lever Type 7	259015 7
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500