

**Garant****Lever lock toolholder, right-hand, Shank / insert size: 32/15mm****Order data**

Order number	250612 32/15
GTIN	4045197861757
Item class	21T

**Technical description**

Shim pins pack	259044 2
Shank size	32 mm
Insert size	15 mm
suitable indexable insert	DN.. 1506..
Head length L <sub>1</sub>	37 mm
Shim	259031 28
Shim punches pack	259047 2
Functional width L <sub>4</sub>	16.8 mm
Overall length L	170 mm
Lever	259015 8
ISO code toolholder	PDNNR/L 3232P15
Lever screw	259018 7
Standard	Works standard
Application type	right-hand
Through-coolant	no
Setting angle $\kappa$	63 degrees

Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

### Accessories

Lever screw Type 7	259018 7
Shim punches set 10 pieces Type 2	259047 2
Shim Type 28	259031 28
Lever Type 8	259015 8
Set of shim pins 10 pieces Type 2	259044 2
Precision Bit for hexagon, 1/4 inch E 6.3 Hexagon 3 mm	674242 3
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500