

Lever lock toolholder, left-hand, Shank / insert size: 25/11 mm



Order data

Order number	250613 25/11
GTIN	4045197861788
Item class	21T

Technical description

Lever screw	259018 6
Overall length L	150 mm
ISO code toolholder	PDNNR/L 2525M11
Insert size	11 mm
Lever	259015 7
Head length L ₁	29 mm
suitable indexable insert	DN.. 1104..
Functional width L ₄	12 mm
Shim pins pack	259044 4
Shim	259031 7
Shank size	25 mm
Shim punches pack	259047 3
Standard	Works standard
Application type	left-hand
Through-coolant	no
Setting angle κ	63 degrees
Application	External longitudinal turning

Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

PrecisionBit for hexagon, 1/4 inch E 6.3 Hexagon 2,5 mm	674242 2,5
Lever Type 7	259015 7
Shim Type 7	259031 7
Lever screw Type 6	259018 6
Shim punches set10 pieces Type 3	259047 3
Set of shim pins10 pieces Type 4	259044 4
Torque screwdriverwith scale, to take interchangeable blades maximum torque 500 cNm	659957 500