

Garant
Lever lock toolholder, left-hand, Shank / insert size: 25/15mm

Order data

Order number	250613 25/15
GTIN	4045197861900
Item class	21T

Technical description

Overall length L	150 mm
Lever	259015 8
Shank size	25 mm
Insert size	15 mm
Shim punches pack	259047 2
Head length L ₁	37 mm
Functional width L ₄	12 mm
Shim	259031 28
ISO code toolholder	PDNNR/L 2525M15
Lever screw	259018 7
suitable indexable insert	DN.. 1506..
Shim pins pack	259044 2
Series	QuickTurn
Standard	Works standard
Application type	left-hand
Through-coolant	no

Setting angle κ	63 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Shim Type 28	259031 28
Set of shim pins 10 pieces Type 2	259044 2
Lever Type 8	259015 8
PrecisionBit for hexagon, 1/4 inch E 6.3 Hexagon 3 mm	674242 3
Lever screw Type 7	259018 7
Shim punches set 10 pieces Type 2	259047 2
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500