

**Garant****Lever lock toolholder, left-hand, Shank / insert size: 32/15mm****Order data**

Order number	250613 32/15
GTIN	4045197861917
Item class	21T

**Technical description**

suitable indexable insert	DN.. 1506..
Shim	259031 28
Insert size	15 mm
Functional width L <sub>4</sub>	16.8 mm
Shank size	32 mm
Overall length L	170 mm
Head length L <sub>1</sub>	37 mm
Shim punches pack	259047 2
Lever	259015 8
Lever screw	259018 7
Shim pins pack	259044 2
ISO code toolholder	PDNNR/L 3232P15
Standard	Works standard
Application type	left-hand
Through-coolant	no
Setting angle κ	63 degrees

Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

### Accessories

Lever Type 8	259015 8
Shim Type 28	259031 28
Shim punches set 10 pieces Type 2	259047 2
Lever screw Type 7	259018 7
Precision Bit for hexagon, 1/4 inch E 6.3 Hexagon 3 mm	674242 3
Set of shim pins 10 pieces Type 2	259044 2
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500