

Garant**Lever lock toolholder, right-hand, Shank / insert size: 25/15mm****Order data**

Order number	251106 25/15
GTIN	4045197861948
Item class	21T

Technical description

Head length L ₁	32 mm
Shim	259031 37
Overall length L	150 mm
Shim pins pack	259044 6
Functional width L ₄	22 mm
Lever	259015 12
ISO code toolholder	PSBNR/L 2525M15
Insert size	15 mm
Shim punches pack	259047 4
Lever screw	259018 11
Shank size	25 mm
suitable indexable insert	SN.. 1506..
Standard	DIN ISO 5610
Application type	right-hand
Through-coolant	no
Setting angle κ	75 degrees

Data sheet

Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500