

**Garant**
**Lever lock toolholder, right-hand, Shank / insert size: 32/19mm**

**Order data**

Order number	251106 32/19
GTIN	4045197861962
Item class	21T

**Technical description**

Insert size	19 mm
Functional width L <sub>4</sub>	27 mm
Lever	259015 13
Shank size	32 mm
Lever screw	259018 13
suitable indexable insert	SN.. 1906..
Shim punches pack	259047 5
ISO code toolholder	PSBNR/L 3232P19
Shim	259031 38
Head length L <sub>1</sub>	39 mm
Overall length L	170 mm
Shim pins pack	259044 7
Series	QuickTurn
Standard	DIN ISO 5610
Application type	right-hand
Through-coolant	no

Setting angle $\kappa$	75 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

---

## Accessories

PrecisionBit for hexagon, 1/4 inch E 6.3 Hexagon 4 mm	674242 4
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500