

Garant
Lever lock toolholder, left-hand, Shank / insert size: 20/12mm

Order data

Order number	251107 20/12
GTIN	4045197861979
Item class	21T

Technical description

Shank size	20 mm
Insert size	12 mm
ISO code toolholder	PSBNR/L 2020K12
Head length L ₁	28 mm
Shim	259031 20
Lever	259015 2
Overall length L	125 mm
Lever screw	259018 2
Functional width L ₄	17 mm
Shim punches pack	259047 2
Shim pins pack	259044 2
suitable indexable insert	SN.. 1204..
Series	QuickTurn
Standard	DIN ISO 5610
Application type	left-hand
Through-coolant	no

Setting angle κ	75 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

PrecisionBit for hexagon, 1/4 inch E 6.3 Hexagon 3 mm	674242 3
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500