

**Garant****Lever lock toolholder, left-hand, Shank / insert size: 25/15mm****Order data**

Order number	251107 25/15
GTIN	4045197861993
Item class	21T

**Technical description**

Shim pins pack	259044 6
Insert size	15 mm
ISO code toolholder	PSBNR/L 2525M15
Shim	259031 37
Shim punches pack	259047 4
Shank size	25 mm
Head length L <sub>1</sub>	32 mm
Overall length L	150 mm
Functional width L <sub>4</sub>	22 mm
Lever screw	259018 11
Lever	259015 12
suitable indexable insert	SN.. 1506..
Standard	DIN ISO 5610
Application type	left-hand
Through-coolant	no
Setting angle κ	75 degrees

## Data sheet

Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

### Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500