



Burr Z3 - medium, with chip breaker, HSS, Type: C1225



Order data

Order number	540800 C1225
GTIN	4045197156099
Item class	52D

Description

Version:

Shank Ø 6 mm.

HSS burrs for difficult vibration applications. **Cylindrical ball nose shape** (WRC)

Application:

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

Technical description

Shape description	ball nose
Overall length	65 mm
Head Ø	12 mm
Shape	C1225
Shank Ø	6 mm
Tooth type abbreviation	Z3
Type of cut	with chip breaker
Toothing grit designation	medium
Head length	25 mm
Series	Tooth configuration Z3
Tool material	HSS
Type of product	Burr

