

**Garant**
**Burr Z9 very coarse (NF/Alu), Carbide, Type: AS1020**

**Order data**

Order number	540709 AS1020
GTIN	4045197522443
Item class	51D

**Description**
**Version:**

Shank Ø 6 mm.

**GARANT** burrs are manufactured from high performance carbide grades with high wear resistance and maximum cutting edge strength, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide. **Shape AS cylindrical(ZYAS), with end cut.**

**Application:**

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

Shank Ø: 6 mm

Shape description: Cylindrical with end cut

Head Ø: 10 mm

Head length: 20 mm

Overall length: 60 mm

Shank Ø: 6 mm

**Technical description**

Head Ø	10 mm
Toothing grit designation	very coarse (NF/Alu)
Shape	AS1020
Shape description	Cylindrical with end cut
Tooth type abbreviation	Z9
Overall length	60 mm

Shank Ø	6 mm
Head length	20 mm
Tool material	Carbide
Type of product	Burr

**User data**

	<b>Suitability</b>	<b>V<sub>c</sub></b>	<b>ISO code</b>
Alu Mg	suitable		
CuZn	suitable		
Plastic, GRP	suitable only under restricted conditions		