

Garant**Burr Z9 very coarse (NF/Alu), Carbide, Type: L1230****Order data**

Order number	540709 L1230
GTIN	4045197522559
Item class	51D

Description**Version:**

Shank Ø 6 mm.

GARANT burrs are manufactured from high performance carbide grades with high wear resistance and maximum cutting edge strength, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide. **Round cone shape** (KEL).

Application:

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

Shank Ø: 6 mm

Shape description: round cone

Head Ø: 12 mm

Head length: 30 mm

Overall length: 70 mm

Shank Ø: 6 mm

Technical description

Toothing grit designation	very coarse (NF/Alu)
Overall length	70 mm
Tooth type abbreviation	Z9
Head Ø	12 mm
Shape	L1230
Shape description	round cone

Shank Ø	6 mm
Head length	30 mm
Tool material	Carbide
Type of product	Burr

User data

	Suitability	V_c	ISO code
Alu Mg	suitable		
CuZn	suitable		
Plastic, GRP	suitable only under restricted conditions		