

Garant**Burr Z1 - coarse, Carbide, Type: D0605****Order data**

| | |
|--------------|---------------|
| Order number | 540600 D0605 |
| GTIN | 4045197155818 |
| Item class | 51D |

Description**Version:**

Shank Ø 6 mm.

GARANT burrs are manufactured from high performance carbide grades with high wear resistance and maximum cutting edge strength, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide. **Ball shape** (KUD)

Application:

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

Technical description

| | |
|---------------------------|------------------------|
| Shape description | Ball |
| Tooth type abbreviation | Z1 |
| Shape | D0605 |
| Toothing grit designation | coarse |
| Head Ø | 6 mm |
| Overall length | 50 mm |
| Shank Ø | 6 mm |
| Head length | 5 mm |
| Series | Tooth configuration Z1 |
| Tool material | Carbide |

Type of product

Burr

User data

| | Suitability | V_c | ISO code |
|-------------------------------|---|----------------------|-----------------|
| Alu Mg | suitable only under restricted conditions | | |
| Steel < 900 N/mm ² | suitable only under restricted conditions | | |
| GG(G) | suitable only under restricted conditions | | |
| CuZn | suitable only under restricted conditions | | |
| Plastic, GRP | suitable only under restricted conditions | | |
| Wood | suitable only under restricted conditions | | |