



Burr Z3 - medium, with chip breaker, HSS, Type: D0807



Order data

Order number	540800 D0807
GTIN	4045197156112
Item class	52D

Description

Version:

Shank Ø 6 mm.

HSS burrs for difficult vibration applications. **Ball shape** (KUD)

Application:

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

Technical description

Shape	D0807
Head Ø	8 mm
Shape description	ball
Overall length	60 mm
Shank Ø	6 mm
Tooth type abbreviation	Z3
Type of cut	with chip breaker
Toothing grit designation	medium
Head length	7 mm
Series	Tooth configuration Z3
Tool material	HSS
Type of product	Burr

