

Garant
Burr Z9 very coarse (NF/Alu), Carbide, Type: AS1625

Order data

Order number	540709 AS1625
GTIN	4045197679802
Item class	51D

Description
Version:

Shank Ø 6 mm.

GARANT burrs are manufactured from high performance carbide grades with high wear resistance and maximum cutting edge strength, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide. **Shape AS cylindrical(ZYAS), with end cut.**

Application:

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

Shank Ø: 6 mm

Shape description: Cylindrical with end cut

Head Ø: 16 mm

Head length: 25 mm

Overall length: 65 mm

Shank Ø: 6 mm

Technical description

Overall length	65 mm
Toothing grit designation	very coarse (NF/Alu)
Shape	AS1625
Head Ø	16 mm
Tooth type abbreviation	Z9
Shape description	Cylindrical with end cut

Shank Ø	6 mm
Head length	25 mm
Tool material	Carbide
Type of product	Burr

User data

	Suitability	V_c	ISO code
Alu Mg	suitable		
CuZn	suitable		
Plastic, GRP	suitable only under restricted conditions		