



Cutting disc Basic* EXTRA THIN, Disc Ø: 230mm



Order data

Order number	563650 230
GTIN	9009012018424
Item class	53T

Description

Version:

General-purpose cutting discs for occasionally cutting off sections, pipes etc.

Specification:

A46BF.

Technical description

maximum speed	6600 min ⁻¹
Disc thickness	1.9 mm
Bore Ø	22.23 mm
Shape description	flat
Specification	A46BF
Disc Ø	230 mm
for material thicknesses	5.7 - 9.5 mm
Grinding medium code	A

Iron, sulphur and chlorine constituents	< 0.1 %
recommended approach angle	90 degrees
optimised for material	Steel
Propulsive equipment	Angle grinders
maximum circumferential speed	80 m/s
Type of product	Cutting disc

User data

	Suitability	V _c	ISO code
Alu Mg	suitable only under restricted conditions		
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
INOX	suitable		
Ti	suitable		
GG(G)	suitable only under restricted conditions		
CuZn	suitable only under restricted conditions		
Plastic, GRP	suitable only under restricted conditions		
Uni	suitable only under restricted conditions		
dry	suitable		

Accessories

Pair of clamping flanges Flange Ø 76 mm	563990 76
---	-----------

