

Garant
Burr Z9 very coarse (NF/Alu), Carbide, Type: C0616

Order data

Order number	540709 C0616
GTIN	4045197522450
Item class	51D

Description
Version:

 Shank \varnothing 6 mm.

GARANT burrs are manufactured from high performance carbide grades with high wear resistance and maximum cutting edge strength, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide. **Shape C cylindrical ball nose** (WRC).

Application:

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

 Shank \varnothing : 6 mm

Shape description: ball nose

 Head \varnothing : 6 mm

Head length: 16 mm

Overall length: 50 mm

 Shank \varnothing : 6 mm

Technical description

Shape	C0616
Head \varnothing	6 mm
Shape description	ball nose
Tooth type abbreviation	Z9
Toothing grit designation	very coarse (NF/Alu)
Overall length	50 mm

Shank Ø	6 mm
Head length	16 mm
Tool material	Carbide
Type of product	Burr

User data

	Suitability	V_c	ISO code
Alu Mg	suitable		
CuZn	suitable		
Plastic, GRP	suitable only under restricted conditions		