

**Garant**
**Burr Z9 very coarse (NF/Alu), Carbide, Type: F1020**

**Order data**

Order number	540709 F1020
GTIN	4045197573605
Item class	51D

**Description**
**Version:**

 Shank  $\varnothing$  6 mm.

**GARANT** burrs are manufactured from high performance carbide grades with high wear resistance and maximum cutting edge strength, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide. Shape F round arch (RBF).

**Application:**

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

 Shank  $\varnothing$ : 6 mm

Shape description: round arch

 Head  $\varnothing$ : 10 mm

Head length: 20 mm

Overall length: 60 mm

 Shank  $\varnothing$ : 6 mm

**Technical description**

Shape description	round arch
Head $\varnothing$	10 mm
Tooth type abbreviation	Z9
Shape	F1020
Overall length	60 mm
Toothing grit designation	very coarse (NF/Alu)

Shank Ø	6 mm
Head length	20 mm
Tool material	Carbide
Type of product	Burr

**User data**

	<b>Suitability</b>	<b>V<sub>c</sub></b>	<b>ISO code</b>
Alu Mg	suitable		
CuZn	suitable		
Plastic, GRP	suitable only under restricted conditions		