



## Burr Z3 - medium, with chip breaker, HSS, Type: D1210



### Order data

Order number	540800 D1210
GTIN	4045197156136
Item class	52D

### Description

#### Version:

Shank  $\varnothing$  6 mm.

HSS burrs for difficult vibration applications. **Ball shape** (KUD)

#### Application:

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

### Technical description

Overall length	60 mm
Head $\varnothing$	12 mm
Shape description	ball
Shape	D1210
Shank $\varnothing$	6 mm
Tooth type abbreviation	Z3
Type of cut	with chip breaker
Toothing grit designation	medium
Head length	10 mm
Series	Tooth configuration Z3
Tool material	HSS
Type of product	Burr

