




Burr Z3 - medium, with chip breaker, HSS, Type: L1230



Order data

Order number	540800 L1230
GTIN	4045197156228
Item class	52D

Description

Version:

Shank \varnothing 6 mm.

HSS burrs for difficult vibration applications. **Round cone shape** (KEL).

Application:

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

Technical description

Overall length	70 mm
Head \varnothing	12 mm
Shape	L1230
Shape description	Round cone
Shank \varnothing	6 mm
Tooth type abbreviation	Z3
Type of cut	with chip breaker
Toothing grit designation	medium
Head length	30 mm
Series	Tooth configuration Z3
Tool material	HSS
Type of product	Burr

