

**Garant**
**Clamping toolholder, right-hand, Shank / insert size: 20/16mm**

**Order data**

Order number	251708 20/16
GTIN	4045197866981
Item class	21T

**Technical description**

Shim	259031 39
Functional width L <sub>4</sub>	25 mm
Head length L <sub>1</sub>	41 mm
Overall length L	125 mm
Shank size	20 mm
Shim screw	259025 3
Screw for clamping claw	259021 1
ISO code toolholder	MVPNR/L 2020K16
suitable indexable insert	VN.. 1604..
Insert size	16 mm
Clamping claw	259038 2
Series	QuickTurn
Standard	Works standard
Application type	right-hand
Through-coolant	no
Setting angle κ	117.5 degrees

Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

---

## Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8
Shim Type 39	259031 39
Clamping claw Type 2	259038 2
Shim screw Type 3	259025 3
Screw for clamping claw Type 1	259021 1
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500