

Garant**Clamping toolholder, right-hand, Shank / insert size: 25/16mm****Order data**

Order number	251708 25/16
GTIN	4045197866998
Item class	21T

Technical description

Insert size	16 mm
Clamping claw	259038 2
Overall length L	150 mm
Shim screw	259025 3
Shank size	25 mm
ISO code toolholder	MVPCR/L 2525M16
Functional width L ₄	32 mm
Shim	259031 39
Screw for clamping claw	259021 1
suitable indexable insert	VN.. 1604..
Head length L ₁	41 mm
Standard	Works standard
Application type	right-hand
Through-coolant	no
Setting angle κ	117.5 degrees
Application	External longitudinal turning

Application	External longitudinal turning
Type of product	Boring bar

Accessories

Clamping claw Type 2	259038 2
Shim Type 39	259031 39
Screw for clamping claw Type 1	259021 1
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8
Shim screw Type 3	259025 3
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500