

Garant**Clamping toolholder, left-hand, Shank / insert size: 25/16mm****Order data**

| | |
|--------------|---------------|
| Order number | 251709 25/16 |
| GTIN | 4045197867124 |
| Item class | 21T |

Technical description

| | |
|---------------------------------|-------------------------------|
| Head length L ₁ | 41 mm |
| Functional width L ₄ | 32 mm |
| ISO code toolholder | MVPCR/L 2525M16 |
| Shim | 259031 39 |
| Overall length L | 150 mm |
| suitable indexable insert | VN.. 1604.. |
| Insert size | 16 mm |
| Clamping claw | 259038 2 |
| Screw for clamping claw | 259021 1 |
| Shim screw | 259025 3 |
| Shank size | 25 mm |
| Standard | Works standard |
| Application type | left-hand |
| Through-coolant | no |
| Setting angle κ | 117.5 degrees |
| Application | External longitudinal turning |

| | |
|-----------------|-------------------------------|
| Application | External longitudinal turning |
| Type of product | Boring bar |

Accessories

| | |
|--|------------|
| Screw for clamping claw Type 1 | 259021 1 |
| Shim Type 39 | 259031 39 |
| PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8 | 674248 TX8 |
| Clamping claw Type 2 | 259038 2 |
| Shim screw Type 3 | 259025 3 |
| Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm | 659957 500 |