

Garant**Burr Z9 very coarse (NF/Alu), Carbide, Type: C1020****Order data**

Order number	540709 C1020
GTIN	4045197522474
Item class	51D

Description**Version:**

Shank Ø 6 mm.

GARANT burrs are manufactured from high performance carbide grades with high wear resistance and maximum cutting edge strength, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide. **Shape C cylindrical ball nose** (WRC).

Application:

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

Shank Ø: 6 mm

Shape description: ball nose

Head Ø: 10 mm

Head length: 20 mm

Overall length: 60 mm

Shank Ø: 6 mm

Technical description

Head Ø	10 mm
Tooth type abbreviation	Z9
Overall length	60 mm
Toothing grit designation	very coarse (NF/Alu)
Shape	C1020
Shape description	ball nose

Shank Ø	6 mm
Head length	20 mm
Tool material	Carbide
Type of product	Burr

User data

	Suitability	V_c	ISO code
Alu Mg	suitable		
CuZn	suitable		
Plastic, GRP	suitable only under restricted conditions		