

**Garant**
**Boring bar, steel, right-hand, Shank  $\varnothing$  / insert size: 40/16mm**

**Order data**

Order number	251720 40/16
GTIN	4045197867162
Item class	21T

**Technical description**

Setting angle $\kappa$	117.5 degrees
Shim	259031 39
Minimum pre-drill $\varnothing D_{\min}$	50 mm
Screw for clamp	259021 1
Clamping claw	259038 2
suitable indexable insert	VN.. 1604..
Overall length L	300 mm
Clamping height $L_2$	38.5 mm
ISO code toolholder	A40T MVPNR/L 16
Centre offset $L_3$	27 mm
Insert size	16 mm
Shim screw	259025 3
Shank $\varnothing D_s$	40 mm
Standard	DIN 8024
Application type	right-hand
Boring depth up to	3xD

Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

---

## Accessories

Clamping claw Type 2	259038 2
Shim Type 39	259031 39
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8
Shim screw Type 3	259025 3
Screw for clamping claw Type 1	259021 1
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500