



## Burr Z3 - medium, with chip breaker, HSS, Type: L1630



### Order data

Order number	540800 L1630
GTIN	4045197156235
Item class	52D

### Description

#### Version:

Shank  $\varnothing$  6 mm.

HSS burrs for difficult vibration applications. **Round cone shape** (KEL).

#### Application:

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

### Technical description

Shape description	round cone
Overall length	70 mm
Head $\varnothing$	16 mm
Shape	L1630
Shank $\varnothing$	6 mm
Tooth type abbreviation	Z3
Type of cut	with chip breaker
Toothing grit designation	medium
Head length	30 mm
Series	Tooth configuration Z3
Tool material	HSS
Type of product	Burr

