



## Burr Z3 - medium, with chip breaker, HSS, Type: C0820



### Order data

Order number	540800 C0820
GTIN	4045197156075
Item class	52D

### Description

#### Version:

Shank Ø 6 mm.

HSS burrs for difficult vibration applications. **Cylindrical ball nose shape** (WRC)

#### Application:

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

### Technical description

Shape	C0820
Overall length	60 mm
Head Ø	8 mm
Shape description	ball nose
Shank Ø	6 mm
Tooth type abbreviation	Z3
Type of cut	with chip breaker
Toothing grit designation	medium
Head length	20 mm
Series	Tooth configuration Z3
Tool material	HSS
Type of product	Burr

