


Garant

Grinding disc (CER), Ø 50.8 mm, Grit: 80



Order data

Order number	553921 80
GTIN	4045197526182
Item class	51E

Description

Version:

Optimum connection between the backing pad and grinding disc by the quick-clamping system (internal thread). Easy and quick disc replacement by hand, even after heavy use.

Sanding disc is centralised, resulting in vibration-free concentricity.

Ceramic grit (CER) ideal for working on stainless steels and nickel alloys. High removal rate and cool cut.

Application:

For efficient sanding down of small areas, even with varying contours in tool, mould and model making, machine, plant and container building. Reduced tool changing times save costs on multi-stage operations.

Note:

Other dimensions and grits available on request.

Technical description

Grit	80
Disc Ø	50.8 mm
Grinding media	Ceramic grit (CER)
Grinding medium code	Ceramic
Product name attribute	Ø 50.8 mm
maximum speed	25000 min ⁻¹
Type of product	Grinding wheel

User data

	Suitability	V _c	ISO code
Alu Mg	suitable only under restricted conditions		
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable only under restricted conditions		
INOX	suitable		
Ti	suitable only under restricted conditions		
GG(G)	suitable		
CuZn	suitable		
Plastic, GRP	suitable		
Wood	suitable		
dry	suitable		

Accessories

Rubber backing pad shank Ø 6 mm medium hard External
Ø 50M mm

553920 50M