

**Garant**

**Blade carrier, concave for face grooving, right-hand, Ø range for groove D1 / D2: 90/130mm**


**Order data**

Order number	273828 90/130
GTIN	4045197867803
Item class	21W

**Description**
**Version:**

Extremely rigid connection and precise clamping due to serrated contact face between the toolholder and clamp.

**Application:**

In conjunction with toolholders No. 273800 to 273811.

**Spare part:**

Clamp screw No. 279815 9.

**Attention:**

Without clamping screws (these are supplied with the toolholders).

**Note:**

$D_1$  = minimum Ø for the first groove /  $D_2$  = maximum Ø for the first cut.

Technology values should be reduced by 30 – 50% depending on the clamping situation and material.

Maximum feed rate 0.025 mm.

Groove width w: 3 mm

maximum cutting depth  $t_{max}$ : 18 mm

**Technical description**

maximum cutting depth $t_{\max}$	18 mm
maximum 1st groove $\varnothing D_2$	130 mm
minimum 1st groove $\varnothing D_1$	90 mm
Application type	right-hand
Groove width w	3 mm
Type of product	Cartridges

## Accessories

Clamping screw Type 9	279815 9
Clamping screw	279910