



Burr Z3 - medium, with chip breaker, HSS, Type: G1225



Order data

Order number	540800 G1225
GTIN	4045197156174
Item class	52D

Description

Version:

Shank \varnothing 6 mm.

HSS burrs for difficult vibration applications. **Gothic arch shape** (SPG).

Application:

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

Technical description

Shape description	Pointed arch
Head \varnothing	12 mm
Overall length	65 mm
Shape	G1225
Shank \varnothing	6 mm
Tooth type abbreviation	Z3
Type of cut	with chip breaker
Toothing grit designation	medium
Head length	25 mm
Series	Tooth configuration Z3
Tool material	HSS
Type of product	Burr

