

Garant**Burr, Carbide, Type: J1613****Order data**

Order number	541000 J1613
GTIN	4045197521910
Item class	51D

Description**Version:**

GARANT burrs are manufactured from high performance carbide grades with high wear resistance and maximum cutting edge strength, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide. Conical shape for **countersinking** and **chamfering**.

Special countersink shape (KSK). Angle 90°.

Application:

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

Note:

Reduced speed for burrs with an overall length of 120 mm: maximum 11,000 rpm

Technical description

Shape	J1613
Overall length	53 mm
Toothing grit designation	medium
Angle	90 degrees
Head Ø	16 mm
Tooth type abbreviation	Z3
Shape description	countersink
Shank Ø	6 mm

Head length	13 mm
Series	Tooth configuration Z3
Tool material	Carbide
Type of product	Burr