

**Garant**
**Boring bar, steel, right-hand, Shank  $\varnothing$  / insert size: 32/16mm**


## Order data

Order number	251724 32/16
GTIN	4045197868206
Item class	21T

## Technical description

Shim screw	259025 3
Screw for clamp	259021 4
Setting angle $\kappa$	93 degrees
Minimum pre-drill $\varnothing D_{\min}$	40 mm
Insert size	16 mm
Shim	259031 39
suitable indexable insert	VN.. 1604..
Clamping height $L_2$	31 mm
Overall length $L$	250 mm
Centre offset $L_3$	22 mm
Clamping claw	259038 4
ISO code toolholder	A32S MVUNR/L 16
Shank $\varnothing D_s$	32 mm
Standard	DIN 8024
Application type	right-hand
Boring depth up to	3xD
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring bar

---

## Accessories

Shim screw Type 3	259025 3
Clamping claw Type 4	259038 4
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8
Screw for clamping claw Type 4	259021 4
Shim Type 39	259031 39
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500