

Garant
Boring bar, steel, left-hand, Shank \varnothing / insert size: 32/16mm


Order data

Order number	251725 32/16
GTIN	4045197868237
Item class	21T

Technical description

Overall length L	250 mm
Shim	259031 39
Setting angle κ	93 degrees
ISO code toolholder	A32S MVUNR/L 16
suitable indexable insert	VN.. 1604..
Centre offset L_3	22 mm
Clamping claw	259038 4
Shim screw	259025 3
Screw for clamp	259021 4
Clamping height L_2	31 mm
Minimum pre-drill $\varnothing D_{\min}$	40 mm
Insert size	16 mm
Shank $\varnothing D_s$	32 mm
Standard	DIN 8024
Application type	left-hand
Boring depth up to	3xD
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring bar

Accessories

Shim screw Type 3	259025 3
Screw for clamping claw Type 4	259021 4
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8
Shim Type 39	259031 39
Clamping claw Type 4	259038 4
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500