

Garant
Boring bar, steel, left-hand, Shank \varnothing / insert size: 40/16mm


Order data

| | |
|--------------|---------------|
| Order number | 251725 40/16 |
| GTIN | 4045197868244 |
| Item class | 21T |

Technical description

| | |
|--|-----------------|
| Shim screw | 259025 3 |
| Overall length L | 300 mm |
| Screw for clamp | 259021 1 |
| Centre offset L_3 | 27 mm |
| Minimum pre-drill $\varnothing D_{\min}$ | 50 mm |
| Insert size | 16 mm |
| Setting angle κ | 93 degrees |
| Clamping height L_2 | 38.5 mm |
| Clamping claw | 259038 4 |
| Shim | 259031 39 |
| suitable indexable insert | VN.. 1604.. |
| ISO code toolholder | A40T MVUNR/L 16 |
| Shank $\varnothing D_s$ | 40 mm |
| Standard | DIN 8024 |
| Application type | left-hand |
| Boring depth up to | 3xD |
| Through-coolant | yes |

| | |
|-----------------|-------------------------------|
| Application | Internal longitudinal turning |
| Type of product | Boring bar |

Accessories

| | |
|--|------------|
| Shim Type 39 | 259031 39 |
| Clamping claw Type 4 | 259038 4 |
| Shim screw Type 3 | 259025 3 |
| PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8 | 674248 TX8 |
| Screw for clamping claw Type 1 | 259021 1 |
| Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm | 659957 500 |