

Garant
Boring bar, steel, left-hand, Shank Ø / insert size: 40/16mm


Order data

| | |
|--------------|---------------|
| Order number | 251729 40/16 |
| GTIN | 4045197868282 |
| Item class | 21T |

Technical description

| | |
|--|-----------------|
| Setting angle κ | 95 degrees |
| ISO code toolholder | A40T MVZNR/L 16 |
| Minimum pre-drill $\varnothing D_{\min}$ | 57 mm |
| Insert size | 16 mm |
| Shim screw | 259025 3 |
| Screw for clamp | 259021 4 |
| Shim | 259031 39 |
| Overall length L | 300 mm |
| Overhang L_1 | 120 mm |
| Clamping height L_2 | 38.5 mm |
| Centre offset L_3 | 35 mm |
| Clamping claw | 259038 2 |
| suitable indexable insert | VN.. 1604.. |
| Usable depth T | 15 mm |
| Shank $\varnothing D_s$ | 40 mm |
| Standard | Works standard |
| Application type | left-hand |

| | |
|--------------------|-------------------------------|
| Boring depth up to | 3xD |
| Through-coolant | yes |
| Application | Internal longitudinal turning |
| Type of product | Boring bar |

Accessories

| | |
|--|------------|
| Shim screw Type 3 | 259025 3 |
| Screw for clamping claw Type 4 | 259021 4 |
| Shim Type 39 | 259031 39 |
| PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8 | 674248 TX8 |
| Clamping claw Type 2 | 259038 2 |
| Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm | 659957 500 |