

**Garant**
**Boring bar, steel, right-hand, Shank  $\varnothing$  / insert size: 40/16mm**

**Order data**

Order number	251728 40/16
GTIN	4045197868268
Item class	21T

**Technical description**

Centre offset $L_3$	35 mm
Clamping height $L_2$	38.5 mm
Screw for clamp	259021 4
ISO code toolholder	A40T MVZNR/L 16
Clamping claw	259038 2
Overhang $L_1$	120 mm
Overall length $L$	300 mm
Setting angle $\kappa$	95 degrees
Shim screw	259025 3
Shim	259031 39
Minimum pre-drill $\varnothing D_{\min}$	57 mm
Insert size	16 mm
suitable indexable insert	VN.. 1604..
Usable depth $T$	15 mm
Shank $\varnothing D_s$	40 mm
Standard	Works standard
Application type	right-hand

Boring depth up to	3xD
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

## Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8
Shim screw Type 3	259025 3
Screw for clamping claw Type 4	259021 4
Shim Type 39	259031 39
Clamping claw Type 2	259038 2
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500