

Garant

T-tap wrench with ratchet long, All-steel, Overall length: 250 mm



Order data

Order number	149000 250
GTIN	4045197861689
Item class	11K

Description

Version:

With two-jaw chuck for clamping square shanks. Moveable T-handle with a groove at each end for engaging the retaining ball. Bracket chrome-plated. Ratchet is reversible and can also be locked. **All-steel construction** for high torque applications. Toolholder with precision concentricity and tight tolerances. Clamping jaws milled and induction hardened for high toughness and optimum surface hardness.

Application:

Suitable for tapping holes where access is difficult.

Note:

The square sizes of other tap and reamer sizes can be found in the tables in the respective Product Groups.

Capacity □: 2.6 - 5.5 mm

for hand taps DIN 352: M3 – M10

Spare jaws No. 148710 size: 85

Technical description

Capacity □	2.6 - 5.5 mm
------------	--------------

Overall length	250 mm
for hand taps DIN 352	M3 – M10
Spare jaws No. 148710 size	85
Material	All-steel
Type of product	Pin vice