




## Grinding disc (A), Ø 25.4 mm, Grit: 80



### Order data

Order number	553925 80
GTIN	4045197331038
Item class	52E

### Description

#### Version:

Optimum connection between the backing pad and grinding disc by the quick-clamping system (internal thread). Easy and quick disc replacement by hand, even after heavy use.

**Aluminium Oxide (A)** for general-purpose use.

Sanding disc is centralised, resulting in vibration-free concentricity.

#### Application:

**For efficient sanding down of small areas, even with varying contours** in tool, mould and model making, machine, plant and container building. Reduced tool changing times save costs on multi-stage operations.

#### Note:

Other dimensions and grits available on request.

### Technical description

Grit	80
Disc Ø	25.4 mm
Grinding media	Regular aluminium oxide (A)
Grinding medium code	A
Product name attribute	Ø 25.4 mm
maximum speed	30000 min <sup>-1</sup>
Type of product	Grinding wheel

## User data

	Suitability	V <sub>c</sub>	ISO code
Alu Mg	suitable		
Steel < 900 N/mm <sup>2</sup>	suitable		
Steel < 1400 N/mm <sup>2</sup>	suitable		
Steel < 55 HRC	suitable only under restricted conditions		
INOX	suitable only under restricted conditions		
GG(G)	suitable only under restricted conditions		
CuZn	suitable		
Plastic, GRP	suitable		
Wood	suitable		
dry	suitable		

## Accessories

Rubber backing pad shank Ø 6 mm medium hard External  
Ø 25M mm

553920 25M