

Garant
Slim hydraulic chuck, BT 30 A = 85, Clamping \varnothing D1: 5mm

Order data

Order number	303446 5
GTIN	4045197868572
Item class	31A

Description
Version:

- **Extremely slim design (3° contour).**
- **Ideal damping characteristics.**
- **Axial length adjustment facility.**
- **Shanks hard turned.**

Application:

- **Especially for tool and mould making.**
- **Wherever reduced interference contours are required.**
- **For drilling, reaming and milling.**
- **For clamping tools with shank tolerance h6.**

Supplied with:

Hexagon socket drive with T-handle.

Optional extras:

Pull studs (PS) No. 308760 – 308802, slotted reducing sleeves No. 302135 – 302187.

Technical description

L ₂	45 mm
Overhang dimension A	85 mm
External \varnothing D	40 mm
\varnothing D ₃	17.7 mm
\varnothing D ₂	13 mm

Clamping $\varnothing D_1$	5 mm
Adapter	BT 30 A = 85
Arbor standard	ISO 7388-2
Arbor standard	JIS B6339
Shape	AD
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	$\leq 3 \mu\text{m}$
Machining strategy	HPC
Machining strategy	HSC
Type of product	Hydraulic clamping chuck

Accessories

Pull stud 45°sealed suitable for steep tapers 30	308760 30
Pull stud 45°sealed suitable for steep tapers 30	308765 30
Pull stud 60°sealed suitable for steep tapers 30	308785 30